

Plug into Power and Convenience with NuTone Inlets.

Turn to the source for power and intelligence. NuTone's line of central cleaning inlets include built-in low-voltage terminals where direct-connect hoses plug right into the inlet – alleviating the need for a power cord. The electrified inlets make it a simple one-step operation to plug in a current-carrying hose. The system turns on automatically when an unswitched hose is inserted or is ready for immediate activation with a switched hose.

NuTone's status indicator hoses and inlets allow for the bag-full or pail-full technology from your power unit for even more convenience. When the light on the power unit changes, indicating that it is time to change the bag or empty the pail, the light on the hose and inlet also changes color. And no additional wiring is needed.

NuTone inlets are the source of ease and convenience when working with a central vacuum system.



Electrified Direct Connect Inlets



Electrified Inlets make it a simple one-step operation to plug in a Current-Carrying hose – no 120V extension cord to carry around. Compatible with NuTone CH615 and CH620 hoses.

CI390 Standard and CI395 Status Indicating

The ElectraValve® Electrified Inlet operates on standard house wiring. It eliminates the need for the extension of electrical cords from the inlet to an electrical outlet. The molded power receptacle clips to a mounting plate and the housing wire is run to the nearest outlet box.

- UL listed Assembly
- Standard:
 - CI390W – White
 - CI390V – Ivory
- Status Indicating:
 - CI395W – White
 - CI395V – Ivory

CI395RK Rough-In Kit

The Electrified Inlet Rough-In Kit includes everything you need to install the CI390 and CI395 inlets. Includes mounting plate, snap-in power receptacle, 6' of 12-gauge cable assembly, plaster guard, CF382S elbow and mounting screws for plaster guard.

CI358 Supervalves

The Supervalve Electrified Inlet operates on standard house wiring. Includes wall valve, rough-in plate with junction box and strain relief.

- UL listed assembly
- CI358W – White
- CI358IV – Ivory

HOW TO CHOOSE:

		Inlet Type								
		CI390	CI395	CI358	CI370	CI335	360	330	CI398	
Hose Type	Current Carrying	CH620	•	•	•					
		*CH520				•	•	•	•	•
		CH615	•	•	•					
		*CH515				•	•	•	•	•
	Low Voltage	372				◦	◦	◦	◦	◦
		CH235				◦	◦	◦	◦	◦
CH230					◦	◦	◦	◦	◦	

* Includes 6 ft. line cord

◦ Limited Function (suction only/non-powered)

• Full Function